


APPLICABLE MOTORS	
MMI P/N	DESCRIPTION
700-1308-02	ASSY, MOTOR, 1000mm, NO RAILS, GEN4, ML
700-1308-05	ASSY, MOTOR, 1000mm, NO RAILS, SYNC, GEN4, ML



DETAIL A
SCALE 1 : 2




3 CHANGED OVERALL WIDTH TOLERANCE, SHT 2
CHANGED OVERALL ENCLOSURE LENGTH TOLERANCE, SHT 2

UNLESS OTHERWISE SPECIFIED		
ALL DIMENSIONS IN MM	SURFACE FINISH [63] 1.6	TOLERANCES
BREAK ALL SHARP EDGES		X.XX ± 0.13
CLEAN AND DEBURR		X.X ± 0.25
USE MIN BEND RADII		X ± 0.5
		DEG ± 0.5°
		TORQUE ± 25%

MAGNEMOTION CONFIDENTIAL
Copyright© 2012 MagneMotion Inc.
The information contained in this drawing is the sole property of MagneMotion Inc. Any reproduction in part or whole without the written permission of MagneMotion is prohibited

INTERPRET DRAWING PER ANSI Y14.5M-1982			
DO NOT SCALE DRAWING	SHEET SIZE B	PROJECT ML	DATE 2011-12-01
CAD PKG. SolidWorks 2011	SCALE 1:1	ENGINEER J MENDENHALL	DRAWN BY J. SYIEK
CAD FILE 701-1308-05.SLDDRW	THIRD-ANGLE PROJECTION		

MagneMotion Inc. 139 Barnum Road Devens, MA 01434 USA (978) 757-9100	TITLE ICD, MOTOR, 1000mm, NO RAILS, GEN4, ML	REV 3
	MATERIAL -	
CAGE CODE 1LR11	DWG NO. 701-1308-05	SHEET 1 OF 2



MagneMotion Inc.
139 Barnum Road
Devens, MA 01434 USA
(978) 757-9100

TITLE	ICD, MOTOR, 1000mm, NO RAILS, GEN4, ML	REV	3
MATERIAL			
DWG NO.	701-1308-05	SHEET 2 OF 2	