



RIGHT ANGLE MALE END VIEW



4-PIN, 7/8-16UN 2B  
RIGHT ANGLE MALE CONNECTOR

SPECIFICATIONS

|                             |   |
|-----------------------------|---|
| CERTIFICATIONS              | UL RECOGNIZED AND CSA CERTIFIED   |
| COUPLING NUT MATERIAL       | EPOXY-COATED ZINC   |
| CONNECTOR OVERMOLD MATERIAL | OIL RESISTANT TPE   |
| CONTACT PLATING             | GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL  |
| CONTACT MATERIAL            | BRASS OR COPPER ALLOY   |
| CABLE TYPE                  | TPE, 18AWG, 300V  |
| CABLE JACKET COLOR          | YELLOW  |
| BEND RADIUS                 | 10 X DIAMETER   |
| NUMBER OF CONDUCTORS [AWG]  | 4x18 AWG  |
| FLEX RATING                 | 5 MILLION CYCLES (BASED ON 10 TIMES CABLE OD)   |
| SHIELDING                   | UNSHIELDED  |
| CABLE RATING                | UL AWM STYLE 20327 VW-1 105C 300V, CSA AWM A/B 1/11 105C 300V FTI, UV OIL AND WATER RESISTANT |
| INGRESS PROTECTION          | NEMA 4, 6P, 12, 13; IP67; 1200 PSI WASHDOWN, IP69K  |
| TEMPERATURE RATING          | -50° ... +105°C (-58° ... +221°F)   |



DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

- NOTES:  
 1. (\*) REPRESENTS THE CABLE LENGTH IN METERS.  
 2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.

|                                     |  |   |                  |
|-------------------------------------|--|---|------------------|
|                                     |  | CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC. |                  |
|                                     |  | Sheet 1 Of 1  |                  |
| 889N-V4HJA-*                        |  | Size  | Ver              |
| Drawn by: LNT      Date: 03/10/2014 |  | C   | 889N-V4HJA-* 0.0 |