


UL OPEN TYPE /
IP00

ESTIMATED WEIGHT MAX:
150 KG (330 LBS)



UL OPEN TYPE /
IP00 WITH GROUNDING
PLATE

ESTIMATED WEIGHT MAX:
155 KG (341 LBS)



UL TYPE 1 /
IP20

ESTIMATED WEIGHT MAX:
160 KG (352 LBS)




UL TYPE 1 /
IP20
WITH C2 FILTER

ESTIMATED WEIGHT MAX:
170 KG (375 LBS)



ALL UNDIMENSIONED GEOMETRIES ARE CONTROLLED BY THE CAD MODEL. IN CASE OF DIMENSION DISCREPANCY, CAD MODEL OVERRIDES.	 Rockwell Automation	CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.
THIRD ANGLE PROJECTION		DATE: 2021-08-21 SHEET 1 OF 5
DESCRIPTION	STANDARD PF755TS.F-6	SIZE DIR VER D 10003954593 03

UL OPEN TYPE / IPOC

PANEL MOUNTING DIMENSIONS






UL OPEN TYPE / IP00
(WITH GROUND PLATE FOR EMC C3 COMPLIANCE)







**TORQUE FOR
GROUNDING PLATE:**

- 53.0 IN-LBS
- 6.0 N·M



UL TYPE 1 / IP20



ALL UNDIMENSIONED GEOMETRIES
ARE CONTROLLED BY THE CAD MODEL.
IN CASE OF DIMENSION DISCREPANCY,
CAD MODEL OVERRIDES.

**Rockwell
Automation**

THIRD ANGLE PROJECTION
DESCRIPTION:

STANDARD PF755TS-F-6

CREATED BY:SMARCIK

CHANGED BY:TPS1

CONFIDENTIAL AND PROPRIETARY INFORMATION
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL
AUTOMATION, INC.

DATE:2021-08-21 SHEET 4 OF 5

SIZE DIR VER

D 10003954593 03

UL TYPE 1 / IP20 WITH C2 FILTER

