



HP AT 208V	HP AT 460V	STYLE	A	B	C	D	E
3 - 10 HP FRAME C	3 - 20 HP FRAME C	A & B	33.13 [841]	39.13 [994]	15.25 [387]	22.50 [572]	37.50 [953]
15 - 20 HP FRAME D (SMALL)	25 - 40 HP FRAME D (SMALL)	A & B	39.13 [994]	39.13 [994]	15.88 [403]	28.50 [724]	37.50 [953]
25 - 30 HP FRAME D (LARGE)		A & B	45.13 [1146]	63.13 [1604]	19.88 [505]	34.50 [876]	61.50 [1562]
	50 - 60 HP FRAME E (SMALL)	A & B	45.13 [1146]	63.13 [1604]	19.88 [505]	34.50 [876]	61.50 [1562]
40 - 50 HP FRAME E (LARGE)	75 - 100 HP FRAME E (LARGE)	A & B	45.13 [1146]	75.13 [1908]	19.88 [505]	34.50 [876]	73.50 [1867]
	125 - 150 HP FRAME F	A & B	45.13 [1146]	75.13 [1908]	19.88 [505]	34.50 [876]	73.50 [1867]

KEY
INCHES
[MILLIMETERS]

DATE	BY	APPROVAL
	DESIGN REVIEW	
	FDR MANUFACTURING	
	AS SHIPPED	
	AS COMMISSIONED	

REV.	DATE	BY	ECN/CR. NO.
A	02/17/06	JCL	
B	8/3/06	JCL	
C	8/14/06	JCL	
D	01/30/08	JCL	
E	8/14/08	ALB	

DR. BY	CHK. BY	ENG. JFH	DWG. NO.	NEXT SH.	SH. NO.
REH/ACI	JCL/ACI		95D01550 -	1	1
DATE 11/14/05	DATE 02/17/06	DATE 11/14/05			

Rockwell Automation

THIS DRAWING IS THE PROPERTY OF ROCKWELL AUTOMATION, INC. OR ITS SUBSIDIARIES AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY ROCKWELL AUTOMATION, INC.

TITLE: DUTY LINE DRAWING - PF400, STYLE A & B
 3-50HP @ 208VAC, 3-150HP @ 460VAC
 NEMA 3R