








- NOTES: DETAIL A
- ENCLOSURE SYSTEM IS 2000MM TALL 600MM DEEP
 - DRIVE SIZE SHOWN:

INPUT VOLTAGE	NORMAL DUTY RATING
400	1650 kW
480	2400 HP
600	2000 HP
690	1800 kW

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED:
DIMENSIONS & TOLERANCING IN ACCORDANCE
WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC
AND CONTROLLED BY THE CAD MODEL AND
CONTROLLED SIMULTANEOUSLY.

DESCRIPTION	 Rockwell Automation		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.		
	STANDARD PF755TR FRAME-11		DATE: 2021-08-24		SHEET 1 OF 2
	CREATED BY: VNS1		SIZE: D1R	VER: 00	
	CHANGED BY: TPI1		D	10006340007	







INPUT BAY
1000MM
(600/690V)

POWER BAY
800MM

POWER BAY
800MM

POWER BAY
600MM

POWER BAY
600MM



NOTES:
1. GROUND BUSBARS ARE 10MM THICK.

DESCRIPTION	STANDARD PF755TR FRAME-11	DATE: 2021-08-24		SHEET 2 OF 2	
		SIZE: D1R		VER	
		D		10006340007	
		CREATED BY: VNS1		CHANGED BY: TPS1	

CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.