




FIBER ROUTING
ENTRY WIRE BAY
400MM





INPUT BAY
1000MM

POWER BAY
800MM

POWER BAY
600MM

POWER BAY
800MM

DC VOLTAGE
BALANCE EXIT
WIRE BAY
400MM



- NOTES:
- ENCLOSURE SYSTEM IS 2000MM TALL AND 600MM DEEP
 - PLEASE CHECK ROCKWELLAUTOMATION.LITERATURE.COM FOR ADDITIONAL INFORMATION ON THE POWERFLEX 755T DRIVES.
 - DRIVE SIZE SHOWN:

INPUT VOLTAGE	NORMAL DUTY RATING
400	2200 kW
480	3600 HP
600	3100 HP
690	2750 kW

DIMENSION IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCING IN ACCORDANCE WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC AND CONTROLLED BY THE CAD MODELS AND CONTROLLED SIMULTANEOUSLY

Rockwell Automation

CONFIDENTIAL AND PROPRIETARY INFORMATION
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

DATE: 2021-08-25

SHEET 1 OF 2

SIZE: D





10006344680

VER: 00

DESCRIPTION: STANDARD PF755TR FRAME-13

CREATED BY: TPS1

CHANGED BY:



NOTES:

1. GROUND BUSBARS ARE 10MM THICK

DIMENSION IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCING IN ACCORDANCE WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC AND CONTROLLED BY THE CAD MODELS AND CONTROLLED SIMULTANEOUSLY



STANDARD PF755TR FRAME-13

DESCRIPTION

CREATED BY:TPS1

CHANGED BY:

CONFIDENTIAL AND PROPRIETARY INFORMATION
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

DATE:2021-08-25 SHEET 2 OF 2
SIZE D1R VER
D 10006344680 00