







IP54 TYPE 12



- NOTES:
- ENCLOSURE SYSTEM IS 2000MM TALL AND 600 DEEP
 - PLEASE CHECK ROCKWELLAUTOMATION.LITERATURE.COM FOR ADDITIONAL INFORMATION ON THE POWERFLEX 755T DRIVES.

2. DRIVE SIZE SHOWN:	INPUT VOLTAGE	NORMAL DUTY RATING
	400	2920 kW
	480	4800 HP
	600	4100 HP
	690	3650 kW

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCING IN ACCORDANCE WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC AND CONTROLLED BY THE CAD MODELS AND CONTROLLED SIMULTANEOUSLY



STANDARD PF755TR FRAME-14

CREATED BY:TPS1

CHANGED BY:

CONFIDENTIAL AND PROPRIETARY INFORMATION
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.


DATE:2020-08-25	SHEET 1 OF 2
SIZE: D1R	VER
D 10006347840	00

CUSTOMER AC
POWER INPUT 2

CUSTOMER AC
POWER INPUT 1

CUSTOMER AC
POWER OUTPUT 2

CUSTOMER AC
POWER OUTPUT 1



FIBER ROUTING
ENTRY WIRE BAY
800MM

INPUT BAY
1000MM

POWER BAY
800MM

POWER BAY
800MM

POWER BAY
600MM

POWER BAY
600MM

DC VOLTAGE
BALANCE EXIT
WIRE BAY
800MM

PE

PE

R/L1
S/L2
T/L3

U/T1
V/T2
W/T3

175.4 TYP


TERMINAL POSITION
CAN BE ADJUSTED

SECTION A-A

PE

140 TYP

350.5 TYP
TERMINAL POSITION
CAN BE ADJUSTED



SECTION B-B

NOTES:
1. GROUND BUSBARS ARE 10MM THICK

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCING IN ACCORDANCE
WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC
AND CONTROLLED BY THE CAD MODELS AND
CONTROLLED SIMULTANEOUSLY



STANDARD PF755TR FRAME-14

CREATED BY:TPS1

CHANGED BY:

CONFIDENTIAL AND PROPRIETARY INFORMATION
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL
AUTOMATION, INC.

DATE:2020-08-25 SHEET 2 OF 2
SIZE D1R VER
D 10006347840 00