



PHASE - NEUTRAL BACK EMF, ENCODER ABSOLUTE POSITION



-30° 0° 30° 60° 90° 120° 150° 180° 210° 240° 270° 300° 330° ELECTRICAL DEGREES

SIN+, SIN-, COS+, COS- ENCODER OUTPUT WAVEFORMS




NOTES:

General Specifications:

1. Motor type: 3 phase, wye winding, permanent magnet rotor, totally enclosed, non-ventilated.	
2. Motor poles:	46
3. Operating Speed, max:	700 RPM
4. Base speed (max speed at peak torque), Ref, at 440 VAC RMS operating voltage:	370 RPM
5. Continuous stall torque, max, at max winding temperature in a 40C ambient:	183 Nm (1620 lb-in)
6. Winding temperature, max, in a 40C ambient:	150 degrees C
7. Continuous stall current, max:	33.2 Amps 0 to peak
8. Heatsink size, aluminum, attached to front mounting flange for continuous torque specifications:	508 x 508 x 19.1mm (20 x 20 x 0.75 inch)
9. Peak stall torque, max:	340 Nm (3009 lb-in)
10. Peak stall current, max:	95.5 Amps 0 to peak
11. Rated Speed (UL file and motor nameplate Rated RPM):	700 RPM
12. Continuous power rating, max:	4.83 kW (6.48 hp)
13. Speed at continuous power rating:	440 RPM
14. Continuous torque, max, at continuous power rating:	105 Nm (929 lb-in)
15. Continuous current, Ref, at continuous power rating:	18.5 Amps 0 to peak
16. Operating voltage, Ref (Not for direct connection to AC line):	480 VAC RMS
17. Insulation class:	155C (Class F)
18. Housing temperature, max:	125C (257F)
19. Ke, +/-10%, phase to phase at 25C +/- 5C:	747 V/kRPM 0 to peak
20. Kt (sine), Ref, at 25C +/- 5C:	6.18 Nm/Amp (54.70 lb-in/Amp) 0 to peak
21. Winding resistance, +/- 10%, phase to phase at 25C +/- 5C:	0.400 ohms
22. Winding inductance, Ref, phase to phase:	6.7 mH
23. Dielectric rating of motor power connections (U,V,W), to ground for 1 second:	2352 VAC RMS 50/60 Hz
24. Audible noise, Ref, at 1 meter distance:	70 dbA
25. Rotor inertia, +/- 10%:	0.123 kg-m ² (1.09 lb-in-sec ²)
26. Friction torque, Ref:	2.2 Nm (19.5 lb-in)
27. Cogging torque, Ref:	1.54 Nm (13.6 lb-in) peak to peak
28. Thermal resistance, Ref, winding to ambient:	0.169 degrees C/watt
29. Thermal time constant, Ref, winding to ambient:	101 minutes
30. Product weight, Ref:	67.6 kg (149 lb)
31. Shipping weight, Ref:	72.1 kg (159 lb)
32. Operating ambient temperature:	0C to 40C (32F to 104F)
33. Storage ambient temperature:	-30C to 70C (-22F to 158F)

Notes:

- "Ref" denotes untoleranced specifications, provided for reference only.
- Speed, torque and current specifications are for operation with Allen Bradley drives.

	CONFIDENTIAL AND PROPRIETARY INFORMATION		Engineering Specification Electrical		Sheet 2 of 4	
	<small>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.</small>		RDB-B41016-3B72AA		Size	10000065579
			Dr. S. Johnson	Date 10-13-09	A	

General Specifications, continued:

- 34. Relative humidity, non-condensing: 5% to 95%
- 35. Liquid / dust protection: IP65
- 36. Shock, max, 6 msec duration: 20 g peak
- 37. Vibration, max, 30 to 2000 Hz: 2.5 g peak
- 38. Bearing arrangement: None internal to motor. Shaft is supported by customer's shaft / bearing system.
- 39. Shaft material: Steel
- 40. Paint color, gloss level, except rear cover: Black, 20 to 35 gloss units
- 41. Rear cover color (Pantone color code), painted or exposed material color: Cool gray # 5, 0 to 20 gloss units
- 42. Shaft, key (if provided), front mounting surface, and connectors are not painted.

Feedback Specifications:

- 1. Feedback interface type (encoder supplier proprietary), order designation: Endat, 2.2/01
- 2. SIN, COS waveform output signals/rev: 2048 sinusoids/rev
- 3. SIN, COS waveform amplitude, measured differentially from SIN+ to SIN-, or COS+ to COS-: 0.75 to 1.2 VAC peak to peak
- 4. SIN, COS voltage offset with respect to ECOM, +/- 0.5 VDC: 2.5 VDC
- 5. DATA+, DATA-, CLK+, CLK- signals applicable standard, signals type: RS 485, Synchronous
- 6. CLK+, CLK- clock frequency, Ref, when operating with Kinetix Endat adapter kit: 468.75 kHz
- 7. Communication hierarchy: Encoder is slave, communication is externally initiated.
- 8. Single turn absolute position value range: 0 to 8191 (13 bit)
- 9. Absolute position data: Binary, value increases with CW shaft rotation viewing motor mounting face.
- 10. Memory storage capacity available for Rockwell parameters, EEPROM, min: 64 words, 16 bits/word
- 11. EPWR 5V (encoder power) input voltage: 3.6 to 14 VDC
- 12. EPWR 5V continuous input current,max, at 5.0 VDC: TBD mA DC
- 13. EPWR 5V inrush input current, max, when connected to Kinetix6000 drive: TBD A DC
- 14. TS+, TS- PTC Thermistor transition temperature, +/-5C: 160 degrees C
- 15. TS+, TS- PTC thermistor circuit resistance, Ref, at thermistor transition temperature: 1100 ohms
- 16. TS+, TS- PTC thermistor circuit resistance, Ref, at 25 C +/- 5C: 160 ohms
- 17. TS+, TS- PTC thermistor resistance vs temperature curves applicable standards: DIN 44081 / 44082
- 18. TS+, TS- PTC thermistor circuit configuration (number of thermistors): 2 in series

Notes:


- 1. "Ref" denotes untoleranced specifications, provided for reference only.

	CONFIDENTIAL AND PROPRIETARY INFORMATION	Engineering Specification Electrical		Sheet 3 of 4	
	THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	RDB-B41016-3B72AA		Size	10000065579
	Dr. S. Johnson	Date	10-13-09	A	Ver 00

**RDB-B41016-3B72AA Performance with 2099-BM06S
at 480 and 400 VAC 3 phase Drive Input, 40C Motor Ambient**

SPEED RPM	TORQUE			
	Tcont	Tpeak 480V	Tpeak 400V	Tpeak 150%
	Nm	Nm	Nm	Nm
0	183	340	340	#N/A
100	178	340	340	#N/A
200	160	340	340	#N/A
335	129	340	340	#N/A
350	126	340	327	#N/A
406	113	340	277	#N/A
500	90.3	270	194	#N/A
590	54.3	202	115	#N/A
590	54.3	202	0	#N/A
600	50.3	195	#N/A	#N/A
700	0	120	#N/A	#N/A
700	#N/A	0	#N/A	#N/A

SPEED RPM	TORQUE			
	Tcont	Tpeak 480V	Tpeak 400V	Tpeak 150%
	lb-in	lb-in	lb-in	lb-in
0	1620	3009	3009	#N/A
100	1575	3009	3009	#N/A
200	1416	3009	3009	#N/A
335	1142	3009	3009	#N/A
350	1115	3009	2894	#N/A
406	1000	3009	2452	#N/A
500	799	2390	1717	#N/A
590	481	1788	1018	#N/A
590	481	1788	0	#N/A
600	445	1726	#N/A	#N/A
700	0	1062	#N/A	#N/A
700	#N/A	0	#N/A	#N/A



Notes:

1. Nm torque values shown are converted from tested lb-in data.
2. "Tpeak 150%" line shown applies when the drive peak current limit is set to 150% of the drive continuous current rating.