

PIN-OUT		
ENCODER CONNECTOR		
PIN	FUNCTION	COLOR
1-6	-	-
7	EPWR	RED
8	ECOM + BAT-	BROWN/BLACK + BLACK
9	SHIELD	BLACK SHRINK
10-11	-	-
12	SD+	BLUE
13	SD-	BLUE/BLACK
14	BAT+	BROWN
15	-	-

PIN-OUT		
POWER CONNECTOR		
PIN	FUNCTION	COLOR
1	U	RED
2	V	WHITE
3	W	BLACK
4	GROUND	YELLOW/GREEN

- SPECIFICATIONS:
- MOTOR TYPE: 8 POLE, 3 PHASE, WYE WINDING, PERMANENT MAGNET ROTOR, TOTALLY ENCLOSED, NON VENTILATED.
  - CONTINUOUS STALL TORQUE: 0.325 Nm (2.88 LB-IN) MAX AT 125°C WINDING TEMPERATURE, IN A 40°C AMBIENT, WHEN MOUNTED ON AN 8 INCH SQUARE X 1/4 INCH THICK ALUMINUM HEAT SINK.
  - OPERATING SPEED: 5000 RPM MAX.
  - Ke: 27 ±10% V/KRPM 0-PEAK (PHASE TO PHASE) AT 20-30°C.
  - SERIAL ENCODER, WITH 16 BIT MULTI-TURN AND 17 BIT SINGLE TURN ABSOLUTE POSITION DATA.
  - FOR ADDITIONAL SPECIFICATIONS SEE TLA130PBJ32AAESE.


POWER CONNECTOR  
AMP 350779-1 HOUSING  
AMP 350218-3 PIN CONTACTS (U,V,W)  
AMP 350654-1 PIN CONTACT (GROUND)

ENCODER CONNECTOR  
AMP 172171-1  
AMP 770835-1 PIN CONTACTS

01	1007016	SJ	RELEASED	-	-
REV	ECN	BY	REVISION DESCRIPTION	DATE	CHKR
UNLESS OTHERWISE SPECIFIED			DRAWN BY	DATE	DESIGN ENGR
DO NOT SCALE DRAWING			SJ	3-09-04	-
DIMENSIONS ARE IN MILLIMETERS			TL-A130P-BJ32AA,ESM		
WITH INCHES REFERENCED [X.X]					
UNTOLERANCED DIMENSIONS ARE REFERENCE					
THIRD ANGLE PROJECTION					

ProE Version 0 Modified 0

DXF FILE AVAILABLE



PART NO.  
TLA130PBJ32AAESM

SCALE : 1  
1.000

DWG SIZE  
B

SHEET  
1 OF 1