

Specifications:				
1. Motor type: 4 pole, 3 phase, asynchronous, ventilated				
2. Base speed: 2965 RPM.				
•				
3. Maximum speed: 5000 RPM.	2			
4. Continuous stall torque: 156 Nm (1381 lb-in) max at 155C winding temperature in a 400				
5. Peak stall torque: 270 Nm (2390 lb-in) max.		(00.0.1 m pM0)		
	2 2970 RPM 124.4 Amps 0 to p	eak max.(88.2 Amps.RMS)		
7. Operating voltage: 460 VAC RMS Ref. (Not for direct connection to AC line).				
8. Continuous stall current: 124.4 Amps 0 to peak max.(88.2 Amps.RMS)		Equivalent circuit parameters		
9. Magnetizing current: 31.4 Amps. RMS ref.				
10. Peak stall current: 217 Amps 0 to peak max.(154 Amps. RMS)		X1: .288 Ohms/phs Ref at 20C to 30C.		
11. Insulation class: 180 (H).		X1: .319 Ohms/phs Ref at 20C to 30C.		
12. Housing temperature: 125C max.		Xm: 7.23 Ohms/phs Ref at 20C to 30C		
13. Winding resistance: .065 Nom. Ohms, phase to phase at 20C to 30C.		R1: .0326 Ohms/phs Ref at 20C to 30C		
Winding inductance: 5.8 mH, phase to phase Ref.		R2: .0227 Ohms/phs Ref at 20C to 30C		
15. Dielectric rating of motor power connections (U,V,W), and thermostat connections				
(TS+, TS-) to ground: 2350 VAC RMS 50/60 Hz for 1 second.				
16. Rotor inertia: .147 kg-m ² Ref.				
18. Product weight: 213 kg (469 lb) Ref.				
19. Operating ambient temperature: 0C to 40C (32F to 104F).				
20. Storage ambient temperature: -30C to 70C (-22F to 158F).				
21. Relative humidity: 5% to 95% non-condensing.				
22. Liquid / dust protection: IP54 with blower installed.				
23. Shock: 10 g peak max, 6 msec duration (18 occurances tested).				
24. Vibration: 2.5 g peak max, 30 to 2000 Hz.				
25. Shaft material: Steel, grade 1040/1045.				
26. Paint: Black. Shaft, key (if provided), flange mounting surface, and connectors are				
not painted.				
not paintoa.				
		TITLE		
	01			
	ES, ELEC, HPK-B1609E-SA42AA			
	REV ES, ELEC, HFR-DT009E-SA4ZAA			
Notes: "Ref" denotes untoleranced specifications, provided for reference only.	 	PART NO.		
	Allon Bradlov	L16M5167ESE		
Speed, torque and current specifications are for motor operation with	Allen-Bradley			
Allen Bradley drives.		A SIZE SHEET 2 OF 4		

Feedback Specifications:

Electrical Hardware:

- 1. SIN, COS waveform output: 1024 sinusoids/rev.
- 2. SIN, COS waveform amplitude: 0.9 to 1.1 Volts peak to peak.
- 3. SIN -, COS voltage offset with respect to power input common: 2.2 to 2.8 VDC.
- 4. +5VDC voltage input: 4.5 to 12.0 VDC.
- 5. +5VDC current input: 125 mA DC max continuous, 1.0 A DC max inrush.
- 6. TS+, TS- thermostat operating voltage: 250 Volts max.
- 7. TS+, TS- thermostat operating current: 1.6/2.5 Amps max at 0.6/1.0 power factor.

Serial Communication:

- 1. DATA+, DATA- signal type, rate: RS 485, 9600 baud, asynchronous.
- 2. Communication hierarchy: Encoder is slave, communication is externally initiated.
- 3. Single turn absolute position value range: 0 to 32,767 steps (12 bit).
- 4. Absolute position data: Binary, value increases with CW shaft rotation viewing motor mounting face.
- 5. Data (byte) format: Start bit, 8 data bits, parity bit, stop bit.
- 6. Memory storage capacity: 128 bytes, EEPROM.
- 7. Encoder temperature data: Binary value of encoder temperature in degrees C.

	01	TITLE					
	01	ES, ELEC, HPK-B1609E-SA42AA					
	REV						
	Allen-Bradley		PART N	0.			
ided for reference only.			L16M5167ESE				
			A SIZE	SHEET	3	OF	4

Note: "Ref" denotes untoleranced specifications, provided for reference only.

