

WAVEFORMS PER CW SHAFT ROTATION VIEWING MOTOR MOUNTING FACE

2.5 VOLT SIGNAL OFFSET WITH RESPECT TO COMMON

RADIAL LOAD CAPACITY (Kgs) - NO AXIAL LOAD - FOR L10 LIFE OF 10,000 HOURS				
Radial Load Capacity at the End of the Shaft (Kgs)				
2500 RPM	1750 RPM	1150 RPM	850 RPM	
350	390	450	500	
AXIAL THRUST CAPACITY (Kgs) - NO RADIAL LOAD - FOR L10 LIFE OF 10,000 HOURS				
Horizontal Mounting Load Capacity at the End of the Shaft (Kgs)				
2500 RPM	1750 RPM	1150 RPM	850 RPM	
250	290	330	360	

01	1021552	VS	RELEASED		
REV	ECN	BY	REVISION DESCRIPTION	CHKR	DATE
PREPARED BY		DATE	DESIGN ENGINEER		DATE
VS		4/4/2006			
TITLE					
ES, ELEC, HPK-B1613E-MB44AA					
Allen-Bradley			PART NO.		
			L16M5199ESE		
			A SIZE	SHEET	1 OF 4

Notes: Print or enlarge waveforms for improved clarity.
For additional specifications see L16M5199ESM.

Specifications:

1. Motor type: 4 pole, 3 phase, asynchronous, ventilated
2. Base speed: 2970 RPM.
3. Maximum speed: 5000 RPM.
4. Continuous stall torque: 237 Nm (2097 lb-in) max at 155C winding temperature in a 40C
5. Peak stall torque: 520 Nm (4062 lb-in) max.
6. Continuous output rating: 73.7 kW (hp) max at 2970 RPM. Continuous current @ 2970 RPM 191 Amps 0 to peak max.(135.3 Amps.RMS)
7. Operating voltage: 460 VAC RMS Ref. (Not for direct connection to AC line).
8. Continuous stall current: 191 Amps 0 to peak max.(135.3 Amps.RMS)
9. Magnetizing current: 54.5 Amps. RMS ref.
10. Peak stall current: 440 Amps 0 to peak max.(312 Amps. RMS)
11. Insulation class: 180 (H).
12. Housing temperature: 125C max.
13. Winding resistance: .033 Nom. Ohms, phase to phase at 20C to 30C.
14. Winding inductance: 2.7 mH, phase to phase Ref.
15. Dielectric rating of motor power connections (U,V,W), and thermostat connections (TS+, TS-) to ground: 2350 VAC RMS 50/60 Hz for 1 second.
16. Rotor inertia: .206 kg-m² Ref.
17. Rotor balancing: Quality grade G-6.3.
18. Product weight: 305 kg (672 lb) Ref.
19. Operating ambient temperature: 0C to 40C (32F to 104F).
20. Storage ambient temperature: -30C to 70C (-22F to 158F).
21. Relative humidity: 5% to 95% non-condensing.
22. Liquid / dust protection: IP54 with blower installed.
23. Shock: 10 g peak max, 6 msec duration (18 occurrences tested).
24. Vibration: 2.5 g peak max, 30 to 2000 Hz.
25. Shaft material: Steel, grade 1040/1045.
26. Paint: Black. Shaft, key (if provided), flange mounting surface, and connectors are not painted.

Equivalent circuit parameters

X1: .136 Ohms/phs Ref at 20C to 30C.
X1: .179 Ohms/phs Ref at 20C to 30C.
Xm : 4.21 Ohms/phs Ref at 20C to 30C
R1: .0164 Ohms/phs Ref at 20C to 30C
R2: .0127 Ohms/phs Ref at 20C to 30C

BRAKE: 460VAC 20Nm max. holding torque

Notes: "Ref" denotes untoleranced specifications, provided for reference only.
Speed, torque and current specifications are for motor operation with Allen Bradley drives.

01	TITLE	
REV	ES, ELEC, HPK-B1613E-MB44AA	
Allen-Bradley	PART NO.	
	L16M5199ESE	
	A SIZE	SHEET 2 OF 4

Feedback Specifications:

Electrical Hardware:

1. SIN, COS waveform output: 1024 sinusoids/rev.
2. SIN, COS waveform amplitude: 0.9 to 1.1 Volts peak to peak.
3. SIN -, COS - voltage offset with respect to power input common: 2.2 to 2.8 VDC.
4. +5VDC voltage input: 4.5 to 12.0 VDC.
5. +5VDC current input: 125 mA DC max continuous, 1.0 A DC max inrush.
6. TS+, TS- thermostat operating voltage: 250 Volts max.
7. TS+, TS- thermostat operating current: 1.6/2.5 Amps max at 0.6/1.0 power factor.

Serial Communication:

1. DATA+, DATA- signal type, rate: RS 485, 9600 baud, asynchronous.
2. Communication hierarchy: Encoder is slave, communication is externally initiated.
3. Single turn absolute position value range: 0 to 32,767 steps (12 bit).
4. Multi-turn absolute shaft revolution value range: 0 to 32,767 revolutions (12bit).
5. Absolute position data: Binary, value increases with CW shaft rotation viewing motor mounting face.
6. Data (byte) format: Start bit, 8 data bits, parity bit, stop bit.
7. Memory storage capacity: 128 bytes, EEPROM.
8. Encoder temperature data: Binary value of encoder temperature in degrees C.

Note: "Ref" denotes untoleranced specifications, provided for reference only.


01	TITLE	
REV	ES, ELEC, HPK-B1613E-MB44AA	
Allen-Bradley		PART NO.
		L16M5199ESE
A SIZE		SHEET 3 OF 4

SPEED RPM	TORQUE		
	Tcont 460V	Tpeak 460V	Tpeak 750 V DC
	Nm	Nm	Nm
0	236.9	459.0	459.0
1000	236.9	459.0	459.0
2300	236.9	459.0	459.0
2500	236.9	429.4	453.9
3000	236.9	352.5	378.5

SPEED RPM	TORQUE		
	Tcont 460V	Tpeak 460V	Tpeak 750 V DC
	lb-in	lb-in	lb-in
0	2097.0	4062	4062
1000	2097.0	4062	4062
2300	2097.0	4062	4062
2500	2097.0	3800	4062
3000	2097.0	3120	3350

Note: Nm torque values shown are converted from tested lb-in data.

**HPK-B1613E-MB44AA Performance with 2099-BM11
at 460 VAC and 750 V DC Drive Input, 40C Motor Ambient**



01	TITLE		
REV	ES, ELEC, HPK-B1613E-MB44AA		
Allen-Bradley		PART NO.	
		L16M5199ESE	
A SIZE		SHEET	4 OF 4