

RADIAL LOAD CAPACITY (Kgs) NO AXIAL LOAD - FOR L10 LIFE OF 10,000 HOURS
Radial Load Capacity at the End of the Shaft (Kgs)

2500 RPM 1750 RPM 1150 RPM 850 RPM 350 390 450 500

AXIAL THRUST CAPACITY (Kgs) NO RADIAL LOAD - FOR L10 LIFE OF 10,000 HOURS
Horizontal Mounting Load Capacity at the End of the Shaft (Kgs)

2500 RPM 1750 RPM 1150 RPM 850 RPM 250 290 330 360

Notes: Print or enlarge waveforms for improved clarity. For additional specifications see 10000000134.

REFE	RENCES	DESCRIPTION		CAD DOCUMENT		
VERSION / CHANGE NUMBER		HPK-E1613E-MA42AA,ESE			CONFIDENTIAL AND PROPRIETARY INFORMATIO  THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIE	
00	10000004		Dool			OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.
		A	utom	kwell ation		PARTS MUST CONFORM TO APPLICABLE ROCKWELL AUTOMATION MANUFACTURING STANDARDS
		DR.	VS	DATE	6/15/2006	SHEET 1 OF 4
						DOCUMENT NUMBER
				<b>I</b>		10000000113

#### Specifications:

- 1. Motor type: 4 pole, 3 phase, asynchronous, ventilated
- 2. Base speed: 2975 RPM.
- 3. Maximum speed: 5000 RPM.
- 4. Continuous stall torque: 237 Nm (2097 lb-in) max at 155C winding temperature in a 40C
- 5. Peak stall torque: 430 Nm (3805 lb-in) max.
- 6. Continuous output rating: 73.7 kW (hp) max at 2975 RPM. Continuous current @ 2975 RPM 242.5 Amps 0 to peak max.(172 Amps.RMS)
- 7. Operating voltage: 460 VAC RMS Ref. (Not for direct connection to AC line).
- 8. Continuous stall current: 242.5 Amps 0 to peak max.(172 Amps.RMS)
- 9. Magnetizing current: 77 Amps. RMS ref.
- 10. Peak stall current: 440 Amps 0 to peak max.(312 Amps. RMS)
- 11. Insulation class: 180 (H).
- 12. Housing temperature: 125C max.
- 13. Winding resistance: .0019Nom. Ohms, phase to phase at 20C to 30C.
- 14. Winding inductance: 1.62 mH, phase to phase Ref.
- 15. Dielectric rating of motor power connections (U,V,W), and thermostat connections (TS+, TS-) to ground: 2350 VAC RMS 50/60 Hz for 1 second.
- 16. Rotor inertia: .206 kg-m2 Ref.
- 17. Rotor balancing: Quality grade G-6.3.
- 18. Product weight: 275 kg (606 lb) Ref.
- 19. Operating ambient temperature: 0C to 40C (32F to 104F).
- 20. Storage ambient temperature: -30C to 70C (-22F to 158F).
- 21. Relative humidity: 5% to 95% non-condensing.
- 22. Liquid / dust protection: IP54 with blower installed.
- 23. Shock: 10 g peak max, 6 msec duration (18 occurances tested).
- 24. Vibration: 2.5 g peak max, 30 to 2000 Hz.
- 25. Shaft material: Steel, grade 1040/1045.
- 26. Paint: Black. Shaft, key (if provided), flange mounting surface, and connectors are not painted.

## Equivalent circuit parameters

X1: .0814 Ohms/phs Ref at 20C to 30C.
X2: ..109 Ohms/phs Ref at 20C to 30C.
Xm: 2.4 Ohms/phs Ref at 20C to 30C
R1: .00973 Ohms/phs Ref at 20C to 30C
R2: .00761 Ohms/phs Ref at 20C to 30C

00		DESCRIPTION					
00							
VER	HPK-E1613E-MA42AA,ESE						
	Rockwell	DOCUMENT N	UMBER				
	Automation 1000000113						
		A SIZE	SHEET	2	OF	4	

Notes: "Ref" denotes untoleranced specifications, provided for reference only.

Speed, torque and current specifications are for motor operation with Allen Bradley drives.


### Feedback Specifications:

#### Electrical Hardware:

- 1. SIN, COS waveform output: 1024 sinusoids/rev.
- 2. SIN, COS waveform amplitude: 0.9 to 1.1 Volts peak to peak.
- 3. SIN -, COS voltage offset with respect to power input common: 2.2 to 2.8 VDC.
- 4. +5VDC voltage input: 4.5 to 12.0 VDC.
- 5. +5VDC current input: 125 mA DC max continuous, 1.0 A DC max inrush.
- 6. TS+, TS- thermostat operating voltage: 250 Volts max.
- 7. TS+, TS- thermostat operating current: 1.6/2.5 Amps max at 0.6/1.0 power factor.

#### Serial Communication:

- 1. DATA+, DATA- signal type, rate: RS 485, 9600 baud, asynchronous.
- 2. Communication hierarchy: Encoder is slave, communication is externally initiated.
- 3. Single turn absolute position value range: 0 to 32,767 steps (12 bit).
- 4. Multi-turn absolute shaft revolution value range: 0 to 32,767 revolutions (12bit).
- 5. Absolute position data: Binary, value increases with CW shaft rotation viewing motor mounting face.
- 6. Data (byte) format: Start bit, 8 data bits, parity bit, stop bit.
- 7. Memory storage capacity: 128 bytes, EEPROM.
- 8. Encoder temperature data: Binary value of encoder temperature in degrees C.




Note: "Ref" denotes untoleranced specifications, provided for reference only.

	TORQUE		
SPEED RPM	Tcont 400V	Tpeak 400V	Tpeak 750 V DC
RPIVI	Nm	Nm	Nm
0	236.9	429.9	429.9
1000	236.9	429.9	429.9
2300	236.9	429.9	429.9
2500	236.9	429.9	429.9
2900	236.9	352.5	429.9
3000	236.9	335.6	378.5

	TORQUE			
SPEED RPM	Tcont 400V	Tpeak 400V	Tpeak 750 V DC	
KFIVI	lb-in	lb-in	lb-in	
0	2097.0	3805	3805	
1000	2097.0	3805	3805	
2300	2097.0	3805	3805	
2500	2097.0	3805	3805	
3000	2097.0	3120	3805	
3000	2097.0	2970	3350	

# HPK-E1613E-MA42AA Performance with 2099-BM11 at 400 VAC and 750 V DC Drive Input, 40C Motor Ambient 460.0 440.0 420.0 400.0 380.0 360.0 340.0 320.0 **Estimated** 300.0 140.0 120.0 Tcont 400V Nm 100.0 MOTOR BASE SPEED 2975 RPM 80.0 Tpeak 400V Nm 60.0 'Tpeak 750 V DC Nm 40.0 20.0 0.0 0 500 1000 1500 2500 3000 2000 SPEED (RPM)



Note: Nm torque values shown are converted from tested lb-in data.