






- NOTES:
- ENCLOSURE SYSTEM IS 2000MM TALL 600MM DEEP.
 - DRIVE SIZE SHOWN:

INPUT VOLTAGE	NORMAL DUTY RATING
400	2000kW
480	3000HP
600	2500HP
690	2300kW


DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED:
DIMENSIONS & TOLERANCING IN ACCORDANCE
WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC
AND CONTROLLED BY THE CAD MODEL AND
CONTROLLED SIMULTANEOUSLY.



STANDARD PF755.TL.TR.FRAME-12
CREATED BY: VNS1
CHANGED BY: TPS1

CONFIDENTIAL AND PROPRIETARY INFORMATION
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL
AUTOMATION, INC.

DATE: 2021-08-25
SHEET 1 OF 2
SIZE: D
VER: 00
10006344103



INPUT BAY
1000MM
(600/690V)


POWER BAY
800MM

POWER BAY
800MM

POWER BAY
600MM

POWER BAY
800MM

POWER BAY
600MM




SECTION A-A

SEE DETAIL B

CUSTOMER OUTPUT PE

137.5


C



NO CUSTOMER CONNECTIONS

DEATIL B


INPUT BAY
1000MM
(400/480V)



NO CUSTOMER CONNECTIONS

DEATIL B

INPUT BAY
1000MM
(600/690V)



55.4
38
38

SECTION C-C

NOTES:

1. GROUND BUSBARS ARE 10MM THICK.



STANDARD PF755 TL TR FRAME-12

CREATED BY: VNS1

CHANGED BY: TPS1

CONFIDENTIAL AND PROPRIETARY INFORMATION
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL
AUTOMATION, INC.

DATE: 2021-08-25 SHEET 2 OF 2

SIZE: D1R VER:

D 10006344103 00